


REV. STATUS SHEETS	REV. LTR.	REVISIONS					
	SHEET NO	LTR	DESCRIPTION	DATE	BY		
	1		Released	3/04/96	JCL		



Materials & Finishes

Center Contact: Silver Plated Beryllium Copper
 Other Metal Parts: Silver Plated Brass
 Backnut: Silver Plated Brass
 Dielectric: Teflon
 Gaskets: Silicone Rubber
 Attachment: Clamp

Electrical Properties

Impedance: 50 Ohms
 Working Voltage: 2700 Volts (RMS max)
 VSWR: 1.20:1 up to 2 GHz
 Insertion Loss: <0.15 dB up to 2 GHz

Unless otherwise specified dimensions in inches. Tolerances are applicable when specified.	Approvals			TIMES MICROWAVE SYSTEMS Wallingford, CT 06492		
	Drawn	JCL	3/04/96	TC-400-716FC Type 7-16 DIN Female Connector for LMR-400		
	Check					
	PrjMg			Size	Code Ident	Dwg.No.
	PrdMg			A	68999	3190-376
	QAMgr			Scale: NA		Sheet: 1 of 1