


SIDE VIEW



Spec	ifications		Notes		Revision History					
Description	Value	Unit			Version	Description			Date	Approved
Technology	Piezo		1) All dimensions are in mm	1	Released from Engineering			10/21/2013	J.S	
Resonant Frequency	3,600	(Hz)	2) All parts meet RoHS							
Rated Voltage	12	(V)								
SPL @ 10cm	88	(dBA)								
Mount Type	Thru Hole									
Voltage Range	3~20	(V)								
Max Rated Current	10	(mA)								
Housing Material	NORYL									
Operating Temperature	-30 ~ +70	°C			Drawn by	Date	Checked by	Date	Approved by	Date
Storage Temperature	-40 ~ +80	°C			A.B.	10/21/2013	C.E.	10/21/2013	J.S	10/21/2013
Weight	5	(g)	DB UNLIMITED	Piezo Transducer	-	TP303612-1				

Additional considerations can be found at www.dbunlimitedco.com/technical-articles.