			Τ						
			Date 03/31/17	SYM	REVISION R	I		DR. B.S.	CK.
NOTES:				'	DIM. 27.20 WAS DIM. 36.00 WAS DIM. 69.10 WAS DIM. 150.0 WAS DIM. 5.0 WAS 3.1 ADDED MOUNTI	35.60 68.70 152.40 18	ι.υ.	ט.ט.	
				G	ADDED BOTTON	M VIEW	T.B.	B.S.	
				Н	DIM. 23.75 WAS	20.45	T.B.	B.S.	
				J	DIM. 23.98 WAS	23.75	T.B.	B.S.	
1. MATERIAL: HOUSING: BLACK POLYPROPYLENE FLAMMABILITY RATING -U.94-HB, UL FILE NO. E216959 TEMPERATURE RANGE: -10°C to +100°C RIVETS: BRASS, NICKLE PLATED. SPRING: SPRING STEEL, NICKLE PLATED. SPRING: SPRING STEEL, NICKLE PLATED. WIRES: 26 AWG, UL1007, CSA, TR-64, 300V, 80°C CONTACT RESISTANCE: UNDER 50mΩ FOR +/- CONTACTS PER EIA-540J000 ROHS 2 COMPLIANT.									
	Tolerance (Except as noted)	MPD Mem	ory	Prote	ection D	evices	, In	С	
		200	Broad H	Iollow Ro	<del>                                     </del>	•			
	decimal					Drawn By			
4.26 [0.17] - 54.80 [2.16]	±.5 (.020)					Approved	l By ]	Г.В.	
	Fractional   Title   ± .8 (.030)   ONE "D" CELL HOLDER WITH WIRE LEADS								
	Angular	Date	Drawing Number						
	± 3°	10/30/18	/30/18 BHDW						