




由Autodesk 教育版产品制作



修 订 REV NO	标 记 MARK	修 改 描 述 REVISION DESCRIPTION	签 名 SIGNATURE	日 期 DATE
		NEW DRG		2016-03-12

**SPECIFICATIONS**  
 Current Rating: 3Amps  
 Insulator resistance: 5000Megohms min.  
 Dielectric Withstanding: AC 500V  
 Operating Temperature: -40° C ~ to +105° C  
 Contact Material: Brass  
 Insulator Material: PA6T  
 Unspecified tolerance: ±0.20

**Dimen Sions List**

Contacts	Dimensions		Contacts	Dimensions	
	A	B		A	B
1*1	2.54	0	1*21	53.34	50.80
1*2	5.08	2.54	1*22	55.88	53.34
1*3	7.62	5.08	1*23	58.42	55.88
1*4	10.16	7.62	1*24	60.96	58.42
1*5	12.70	10.16	1*25	63.50	60.96
1*6	15.24	12.70	1*26	66.04	63.50
1*7	17.78	15.24	1*27	68.58	66.04
1*8	20.32	17.78	1*28	71.12	68.58
1*9	22.86	20.32	1*29	73.66	71.12
1*10	25.40	22.86	1*30	76.20	73.66
1*11	27.94	25.40	1*31	78.74	76.20
1*12	30.48	27.94	1*32	81.28	78.74
1*13	33.02	30.48	1*33	83.82	81.28
1*14	35.56	33.02	1*34	86.36	83.82
1*15	38.10	35.56	1*35	88.90	86.36
1*16	40.64	38.10	1*36	91.44	88.90
1*17	43.18	40.64	1*37	93.98	91.44
1*18	45.72	43.18	1*38	96.52	93.98
1*19	48.26	45.72	1*39	99.06	96.52
1*20	50.80	48.26	1*40	101.6	99.06

**深圳市华德共创科技有限公司**  
 Shenzhen Huade co-create Technology Co., LTD  
 电话: 0755-27111216 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表			TITLE: 产品名称: 2.54X8.5单排直插排母PC3.0			
X.X ±0.30	X.X° ±3°	APPD: 核准:	PART NO: 产品编号: HDGCPH2.54-PZS-01-n			
X.XX ±0.20	X.XX° ±2°	CHECK: 校对: 王建业	DATE	SCALE	UNIT	CODE NUMBER
X.XXX ±0.10	X.XXX° ±1°	DRAW: 绘图: 黄艳兰	2016-03-12	1:1	mm	A001

由Autodesk 教育版产品制作