

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE






COMMON TOLERANCE	
X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED	
DRAWN BY	FUYUAN	CHECKED BY	COCO
DATE	2019	APPROVAL	B ALEN
ROCPCU TECHNOLOGY CO., LTD			

PRODUCT NAME:	
MODEL NO:	TP91214P124RAB
Https:	www.rocpcu.tw
<small>Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission</small>	

	A	B	C	D	E	F	G
1	性能参数			13. Compression torque: ≤ 3N 按压扭力: ≤3N			
	1. Heating current: Ui: AC250V, Ith: 3A 发热电流: Ui: AC250V, Ith: 3A			14. Electrical life: 500000 cycles 电气寿命: 500000 cycles			
	2. Rated current: 2A/DC36V 额定电流: 2A/DC36V			15. mechanical: 500000cycles 机械寿命: 500000cycles			
	3. Insulation resistance: ≥1000MΩ 绝缘电阻: ≥1000MΩ			16. Operation method: Self-locking 操作方式: 自锁式			
	4. Contact resistance: ≤50mΩ 接触电阻: ≤50mΩ			17. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N			
	5. Pressing stroke: 2.30mm ± 0.10 按压行程: 2.30mm ± 0.10			18. LED lamp power consumption: 20m以下 LED灯功耗: 20m以下			
2	6. Contact stroke: 1.00mm ± 0.10 接触行程: 1.00mm ± 0.10			19. LED lamp lifespan: 40000h LED寿命: 40000h			
	7. welding temperature: 320 °C ± 20 °C 焊接温度: 320 °C ± 20 °C			20. LED color: Red LED颜色: 红色			
	8. Welding duration: Less than 3 seconds in duration 焊接时长: Less than 3 seconds in duration						
	9. Nut assembly torque: 5-14N 螺帽装配力矩: 5-14N						
	10. Protection level: IP65 防护等级: IP65						
3	11. Explosion prevention level: IK08 防暴等级: IK08						
	12. Working environment temperature: -20 °C ~ +55 °C 工作环境温度: -20 °C ~ +55 °C						
4							

A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3					X.XX	± 0.10	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91214P124RAB
A2					X.X	± 0.15	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X	± 0.25	ROCPCU TECHNOLOGY CO., LTD				
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR					
	A	B	C	D	E	F	G				


A	B	C	D	E	F	G
材质参数						
10	luminous zone 发光区	PC 塑料	1			
9	LEDpin LED脚	Brass 黄铜	1		Silvering 镀银	
8	Base 底座	PA66	1		Black 黑色	
7	Pin 引脚	Brass 黄铜	1		gold-plating 镀金	
6	Contact material 接触材质	Silvering 镀银	1			
5	Base 基座	PA66	1		Black 黑色	
4	Arm nut 固定螺帽	Brass 黄铜	1		nickeling 镀镍	
3	Oring O型圈	Silica gel 硅胶	1			
2	Housing 外壳	Aluminum alloy 铝合金	1		Oxidized/Black 氧化/黑色	
1	Key 按键	Aluminum alloy 铝合金	1		Oxidized/Black 氧化/黑色	
NO 序号	Part name 部件名	Material 材料		QTY 数量		Remark 备注
A4				UNIT	MM	PROJECTED 
A3				DRAWN BY	FUYUAN	CHECKED BY
A2				DATE	2019	APPROVAL B
A1						ALEN
REV	DATE	REVISION	DESCRIPTION	ISSUE	ROCPU TECHNOLOGY CO.,LTD	
					Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission	

材质参数



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED		PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91214P124RAB
DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw

ROCPU TECHNOLOGY CO.,LTD

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission