





A4					 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3						X.XX	± 0.10	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91222P224RS
A2						X.X	± 0.15	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1						X	± 0.25	ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION	ISSUE		ANGULAR	—					
	A		B		C		D	E	F	G		



性能参数

1. Heating current: Ui: AC220V, Ith: 50mA
发热电流: Ui: AC220V, Ith: 50mA
2. Rated current:0.10A/DC36V
额定电流:0.10A/DC36V
3. Power-frequency withstand voltage:2000V1min
工频耐压:2000V1min
4. Insulation resistance:≥50MΩ
绝缘电阻 :≥50MΩ
5. Contact resistance:≤50mΩ
接触电阻 :≤50mΩ
6. Pressing stroke:0.50mm ± 0.10
按压行程:0.50mm ± 0.10
7. Contact stroke:0.50mm±0.10
接触行程 :0.50mm±0.10
8. welding temperature: 320 °C± 20 °C
焊接温度: 320 °C± 20 °C
9. Welding duration: Less than 3 seconds in duration
焊接时长: Less than 3 seconds in duration
10. Nut assembly torque:5-14N
螺帽装配力矩:5-14N
11. Protection level:IP67
防护等级:IP67
12. Explosion prevention level: IK08
防暴等级: IK08
13. Working environment temperature: -20 °C~+55 °C
工作环境温度: -20 °C~+55 °C
14. Compression torque: ≤ 3N
按压扭力: ≤3N
15. Electrical life: 200000 cycles
电气寿命: 200000 cycles
16. mechanical: 1000000cycles
机械寿命: 1000000cycles
17. Operation method:Unlocking
操作方式: 无锁式
18. NO reverse thrust foot torque: ≤30N
NO反推脚扭力: ≤30N
19. LED lamp power consumption: 20m以下
LED灯功耗: 20m以下
20. LED lamp lifespan: 40000h
LED寿命: 40000h
21. LED color: Red
LED颜色: 红色

A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3					X.XX	± 0.10	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91222P224RS
A2					X.X	± 0.15	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X	± 0.25	ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR					
		A	B		C		D	E	F	G	

材质参数

9	luminous zone 发光区	PC 塑料	1		
8	LEDpin LED脚	Brass 黄铜	1	Silvering 镀银	
7	Pin 引脚	Brass 黄铜	1	gold-plating 镀金	
6	Contact material 接触材质	silver alloy 银合金	1	Silvering 镀银	
5	Base 基座	PBT	1		
4	Arm nut 固定螺帽	Brass 黄铜	1	nickeling 镀镍	
3	Oring O型圈	Silica gel 硅胶	1		
2	Housing 外壳	SUS 不锈钢	1		
1	Key 按键	SUS 不锈钢	1		
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注	

A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3					X.XX	± 0.10	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91222P224RS
A2					X.X	± 0.15	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X	± 0.25	ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission			