

## BU-32603-@

(Shrouded Banana Plug)



- Mueller's BU-32603-@ is a shrouded Banana plug that is field assembled and is IEC 1010 compliant Banana plug.
- Fits 4mm Banana jacks that accepts shrouded Banana plugs.
- Easy Solder connection with wire between 18-14 AWG.
- Material:
  - Housing Nylon
  - Contact Nickel plated Brass and Beryllium Copper
- Ratings:
  - o 20 Amps
  - o 1000 V Cat III
  - o 1500 V Cat II
- Color: The "@" in the model number represents color. Available colors:
  -0 Black, -2 Red, -4 Yellow, -5 Green, -6 Blue, -9 White
- RoHS 3 Compliant

Toll Free: 800.955.2629

Phone: 330.780.2525

Fax: 330.780.2524



## **Assembly Photo (Wire not included)**

- 1) Slide threaded nut, and strain relief onto wire
- 2) Solder wire to banana plug
- 3) Assemble all parts and thread nut into shroud

Toll Free: 800.955.2629

Phone: 330.780.2525

Fax: 330.780.2524