

BU-P1825-@
(Solderless Stackable Banana Plug)



- The BU-P1825 is a solderless, stackable 4mm banana plug. Useful for applications where solder or crimping cannot be used or where temporary wire connection is desired.
- Overall length 1.55" (39.3mm), wire port ID = 0.17" (4.3mm), set screw port ID = 0.17" (4.3mm)
- Can be attached to wire as small as 22 AWG and as big as 18 AWG via a small set screw. Wire enters from the side.
- Material: Banana plug Nickel-plated beryllium copper
 Insulator Polypropylene
- Ratings: Current 15 Amps
 Voltage Hands-free testing to 5000 VRMS
 Temperature Up to 122°F (50°C)
- Color: The "@" in the part number represents color. Available colors are:
 -0 Black, -1 Brown, -2 Red, -3 Orange, -4 Yellow,
 -5 Green, -6 Blue, -7 Violet, -8 Gray, -9 White
- RoHS 3 compliant, exemption 6c