395-ISA SERIES

Card Edge Connectors 0.100" (2.54mm) Pitch

cardEDG

Features:


- For Industry Standard Architecture
- 0.100" (2.54mm) contact spacing x 0.200" (5.08mm) row spacing
- Accepts 0.062" (1.57mm) nominal thickness P.C. board
- High profile insulator body, 0.600" (15.24mm) divided in groups of 62 and 36 contacts
- Contact termination options include P.C. tail, wire wrap, 90 degree and extender board bends
- Automatic wire wrap positioning holes
- Accepts between contact and in-contact polarizing keys
- **RoHS Compliant & UL Certified**



Specifications:

Insulator Material	UL 94V-0 Thermoplastic Polyester, Black Color	
Contact Material	Copper Alloy	
Contact Plating	Gold Plating on mating area and Tin Plating on tails with Nickel underplating all over	
Current Rating	3 amps	
Contact Resistance	10 milliohms maximum	
Dielectric Withstanding Voltage	1200 V AC rms at sea level between adjacent contacts	
Insulation Resistance	5000 megaohms minimum	
Operating Temperature	-40°C to +105°C	
Insertion Force	16 oz (4.45 N) maximum per contact pair when tested with .070" (1.78mm) thick gauge	
Withdrawal Force	1 oz (0.28 N) minimum per contact pair when tested with .054" (1.37mm) thick gauge	

Example Part Number:	395-098-520-300	Contact Code:	Tail Description:	Tail Size:	Tail Length "G":
	T T T T	520	P.C. Tail	.030 x .018 (0.76 x 0.46)	.175 (4.45)
Series —		521	P.C. Tail	.025 Square (0.64 Square)	.150 (3.81)
Total Number of Contacts —		523	P.C. Tail	.025 Square (0.64 Square)	.390 (9.91)
Contact Code —————Variation Code		524	P.C. Tail	.018 Square (0.46 Square)	.175 (4.45)
variation Code		525	P.C. Tail	.018 Square (0.46 Square)	.150 (3.81)
Series:		540	Wire Wrap	.025 Square (0.64 Square)	.560 (14.22)
395		541	Wire Wrap	.025 Square (0.64 Square)	.750 (19.05)
Total Number of Contacts:		542	Wire Wrap	.025 Square (0.64 Square)	.645 (16.38)
098		544	Wire Wrap	.050 x .025 (1.27 x 0.64)	.750 (19.05)
Variation Code:	Description:	556	EXTENDER BOARD BEND	(CODE 520 CONTACTS)	
300	Card Slot Barrier Divides	558	90 DEGREE BEND	(CODE 541 CONTACTS)	
	the 98 Contacts into Groups of 62 and 36	559	90 DEGREE BEND	(CODE 541 CONTACTS)	
		560	EXTENDER BOARD BEND	(CODE 523 CONTACTS)	








Card Edge Connectors 0.100" (2.54mm) Pitch







NUMBERED SIDE, EVEN NUMBERED SIDE OR ROW "A" SIDE OF CONNECTOR (DEPENDING ON THE SERIES) .060 (1.52) .150 (3.81) THIS CONTACT ROW IS STANDARD FOR SINGLE ROW BEND

CONTACT CODE 558

CONTACT CODE 559





CONTACT CODE 556

CONTACT CODE 560

CONTACT CODE	Α	В	
556	0.170(4.32)		
558	0.235(5.97)	0.635(16.13)	
559	0.285(7.24)	0.635(16.13)	
560	0.375(9.53)		



