

Contact Dimensions: 540-Wire Wrap .025 Sq.(0.64 Sq.) - Tail LG=.560(14.22) .100 (2.54) Contact Spacing x .200 (5.08) Row Spacing





.160[4.06] POINT OF CONTACT .330[8.38] CARD SLOT 50 [3.81] SECTION A-A

345/395 SERIES CARD EDGE CONNECTOR PART NUMBER: 395-062-540-208

YOUR CONNECTION TO QUALITY & SERVICE

ACAD REFERENCE NO. 345-ENG-MASTER		
DRAWN: R.STA.MONICA	DATE:MAY.16/2017	
CHECKED:	DATE:	
SCALE: 1:1	SHEET 1	OF 2
DRAWING NUMBER		ISSUE
345-ENG-MASTER		1

CONTACT MATERIAL; COPPER TIN ALLOY CONTACT PLATING: GOLD ON THE MATING AREA, TIN PLATING ON THE CONTACT TAILS, NICKEL UNDERPLATE

INSULATOR MATERIAL: THERMOPLASTIC PBT BLACK, UL 94V-0











Contact Code 558

Contact Code 559

Contact Code 560

INSULATOR MATERIAL: THERMOPLASTIC POLYESTER, UL 94V-0

DAP MATERIAL AVAILABLE UPON REQUEST

CONTACT MATERIAL; COPPER ALLOY

CONTACT PLATING: GOLD ON THE MATING AREA, TIN PLATING ON THE CONTACT TAILS, NICKEL UNDERPLATE

345/395 SERIES CARD EDGE CONNECTOR CONTACT CODE 555,556,558,559,560 DIMENSIONS

YOUR CONNECTION TO QUALITY & SERVICE

ACAD REFERENCE NO. 345-ENG-MASTER DATE:MAY.16/2017 DRAWN: R.STA.MONICA 1:1 SHEET 2 OF 2

345-ENG-MASTER