


			1		
	Part Number:		DRAWN	_,,_,_,	
	TP453212-1		CJ	7/17/2015	
	1745.	0212-1	CHECKED	12/11/2015	
			P.D	12/11/2015	
	Description:	ansducer	APPROVED	12/11/2015	
FIEZU III	ansuucei	J.S	12,11,2010		

This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com

Side View




PA66


Housing Material

Weight

Top View



Bottom View



4) Subject to change or redrawn without notice

Items	Specifications	Conditions						
Sound Pressure Level	110	dB (@ 10cm)						
Resonant Frequency	3,200	Hz		REVISION HISTORY				
Rated Voltage	12	V	REV	DESCRIPTION	DATE	APPROVED		
Voltage Range	1 ~ 40	V		Released from Engineering	10/21/2013	J.S.		
Capacitance	25,000	pF (±30% at 120 Hz)	1	Update Operating/Storage Temp	3/3/2015	C.E.		
Max. Rated Current	7	mA	2	Updated to new template	12/11/2015	J.S.		
Storage Temperature	-50 ~ +105	°C		NOTES				
Operating Temperature	-50 ~ +105	°C		All dimensions are in mm unless otherwise noted				
Connection Method	Plate			2) All tolerances are ± 0.5 mm unless otherwise noted				
Mount Type	Thru-hole			3) All parts meet RoHS				