

# MICRO SWITCH

FREEPORT ILLINOIS, U.S.A.  
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

## SWITCH - BASIC

V3-1113

CK-MI350

CATALOG LISTING

S

V3-1113

M

DRAWING NUMBER

X

ISSUE

4

REPLACES X61345-V3

RELEASE NO. PR-4024

CHECK

CHECK

CHECK


CHECK

CHECK

CHECK

CHECK

CHECK



NOTE -  
1 - TERMINALS ARE PLATED FOR SOLDERING

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE — — — 75 GRAMS MAX	CONTACT ARRANGEMENT S P D T	DO NOT SCALE PRINT
RELEASE TRAVEL — — — — .010 MIN	L112 10A 1/3HP 125 OR 250 VAC 1/2A 125 VDC, 1/4A 250 VDC 4A 125 VAC "L"	UNLESS OTHERWISE NOTED
RELEASE FORCE — — — — 10 GRAMS MIN		DIMENSIONS ARE IN INCHES
DIFFERENTIAL TRAVEL — — — .002-.010		<b>TOLERANCES ARE</b>
OVERTRAVEL — — — — .050 MIN		ONE PLACE (.01) ± .030
FREE POSITION — — — — .625 MAX		TWO PLACE (.00) ± .015
		THREE PLACE (.000) ± .005
		ANGLES ±
		WEIGHT



FO-52848

DRAWN

D B W 20 MAR 74 CHECK L S D 121 MAR 74 CHECK