





2

1

3

NOTES:

- 1. MATERIAL:
 - (A). TERMINAL: COPPER (STOCK THICKNESS .031±.001 [0.79])

22:51:25

10

- PLATING: ELECTRO-TIN (.0003 MIN.)
- (B). INSULATION: MOLDED PVC (BLUE)
- 2. MWID: MAXIMUM WIRE INSULATION DIAMETER
- 3. WIRE SIZE: 16 -14 AWG
 - 1.0 -2.5 MM²
- 4. "UL" LISTING #E32244
- "CSA" LISTING #18689
- 5. ALL DIMENSIONS IN INCHES/[MM].
- 6. PARTS ARE ROHS COMPLIANT.
- 7. DIMS. SHOWN ARE FOR REFERENCE ONLY.

DOCUMENT STATUS | P1 | RELEASE DATE | 2019/10/18

