

^{3.} THIS PRODUCT IS ROHS COMPLIANT. EACH BAG IS TO BE MARKED WITH ROHS COMPLIANT LABEL OR EQUIVALENT MARKINGS. LED MUST BE Pb FREE.

4. MOISTURE SENSITIVITY LEVEL IS 3.

260

-40 TO +85

-40 TO +85

3000

°C

°C

°C

V

REFLOW SOLDERING TEMPERATURE FOR IO SEC

ELECTROSTATIC DISCHARGE THRESHOLD (HBM)

OPERATING TEMPERATURE

STORAGE TEMPERATURE

REVISIONS	DRN	CKD	APP	QA	СМ	DATE
NEW RELEASE	LD		NO			3-8-22
CATIONS (units : mm)						

THIS DRAWING AND THE CONTENTS HEREIN ARE CONFIDENTIAL AND THE SOLE PROPERTY OF DIALIGHT CORP. REPRODUCTION OF THIS DRAWING OR CONSTRUCTION OF ANY PARTS WITHIN THIS DRAWING ARE FORBIDDEN WITHOUT THE WRITTEN CONSENT OF DIALIGHT CORP.					
DIALIGHT CORP INTERNAL REFERENCE ONLY = 3D MODEL : 4500597230219					
SCALE: 12.000	DRAWING NUMBER	REV			
ALL DIM's: INCH (mm)		Δ			
TOLERANCES:	C-18553	A			

UNLESS OTHERWISE SPECIFIED	
FRACTIONS: ±1/64 DECIMALS (.XX): ±.01 DECIMALS (.XXX): ±.005	SM RIGHT ANGLE GREEN
DECIMALS (.XXXX): ±.0005 ANGLES: ±1°	MATERIAL
FINISH	Dialight ISOL ROUTE 34 SOUTH FARMINGDALE, NJ 07727 (732) 919-3119 www.dialight.com
FSCM 83330	SHEET I OF I FAMILY TABLE: