



1700 - 1850 MHz Cavity Bandpass Filter

Part Number: AB1775B1236



ANATECH ELECTRONICS INC
RF & Microwave Filters & Products

Electrical specifications

Frequency Range: 1700 ~ 1850 MHz

Insertion Loss: =/ $<$ 1.0 dB

Return Loss: =/ $<$ 15 dB

Rejection 1: =/ $>$ 40 dB@1650MHz

Rejection 2: =/ $>$ 40 dB@1900MHz

Mechanical

Mounting Method: Threaded Mounting

Connector Type: SMA (F)

Dimensions: 3.11"x1.46"x1.58"

Surface Finish: black

Environmental

Operating Temperature: -45°C to +85°C

Storage Temperature: -55°C to +100°C

Outline Drawing:

