# Precision Test Adapters

## 1.85 mm(M) to 1.85 mm(F)



**Withwave's Precision Test Adapters** are designed based on precision microwave interconnection technologies.

This 1.85 mm(M) to 1.85 mm(F) adapter is manufactured to precise microwave specifications and constructed with male gender on side 1 and female gender side 2.

The precision microwave connector interfaces ensure an excellent microwave performance up to 67 GHz



#### Features

- Frequency range : DC to 67 GHz- VSWR : 1.25 : 1(Max) @ 67 GHz

- Stainless steel (passivated)

### Specification

Scope	Specification	AD01M01FS1
Electrical	Impedance(Ohm)	50
	Operation Freq.(GHz)	DC to 67 GHz
	VSWR (Max)	1.25 : 1
Material	Dielectric	Special dielectric
	Center Contact	Beryllium copper with gold plated
	Body	Passivated Stainless Steel

<sup>\*</sup> RoHS Compliant


# Precision Test Adapters

## 1.85 mm(M) to 1.85 mm(F)



## Drawing

Part No.: AD01M01FS1



### Test Result

#### ■ Frequency: 10 MHz to 65 GHz

