

TEMPERATURE RANGE: -10°C to +100°C SPRINGS: SPRING STEEL, NICKEL PLATED

RIVETS: BRASS, NICKEL PLATED

WIRES: 26 AWG, UL1007, CSA-TR-64, 300V, 80°C

CONTACT RESISTANCE: UNDER  $50m\Omega$  FOR +/- CONTACTS

PER EIA-540J000

**ROHS 2 COMPLIANT** 

## MOUNTING INSTRUCTION:

USE 2-56 MACHINE SCREWS OR EYELETS 0.089" OD BY 0.15" FLANGE STIMPSON GS-3 SERIES OR EQUIVALENT. ALSO ADHESIVES AND DOUBLE SIDED TAPES WORK WELL.

Tolerance (Inches)	MPD Memory Protection Devices, Inc 200 Broad Hollow Road, Farmingdale, New York 11735			
Decimal			Scale	Drawn By B.S.
±.5 (.020)				Approved By T.B.
Fractional ± .8 (.030)	Title TEN "AA" CELL HOLDER WITH WIRE LEADS			
Angular ± 3°	Date 06/30/17	Drawing Number BH10AAW		