


Weight: 1.65g

NOTES:

MATERIAL: GLASS FILLED NYLON 66, UL94V-0
 COLOR BLACK, UL FILE NO. E196894
 CONTACTS: PHOSPHOR BRONZE, C5191, NICKEL PLATED
 ELECTRICAL :
 VOLTAGE: 250V AC
 CONTACT RESISTANCE: 30m Ω MAX
 INSULATION RESISTANCE: 1000m Ω AT DC 500V
 DIELECTRIC STRENGTH: AC 1000V PER MINUTE
 TEMPERATURE RANGE: -40°C TO +200°C
 ROHS COMPLIANT

Date	SYM	REVISION RECORD	AUTH	DR.	CK.
10/18/19	B	Added weight of the part	T.B.	B.S.	
08/30/23	C	Dim. 5.84 was 5.80 Dim. 23.39 was 23.42 Dim. 13.21 was 13.10 Added Dim. 0.76	D.L.	B.S.	
09/06/23	D	Dim. 5.08 was 5.00 Dim. 10.16 was 10.00 Dim. 3.81 was 3.60 Updated View	D.L.	B.S.	

Tolerance (Except as noted)	 Memory Protection Devices, Inc 200 Broad Hollow Road, Farmingdale, New York 11735			
decimal $\pm .5$ (.020)	Scale	Drawn By B.S.		
Fractional $\pm .8$ (.030)	Title BR/CR/DL 2032 VERTICAL BATTERY HOLDER, 3 PINS			
Angular $\pm 3^\circ$	Date 09/06/23	Drawing Number BK-5058-4MM		
Approved By T.B.				