


		1		
Part Number:		DRAWN	10/15/2021	
NAVAIOC	4202.2	CJ	10/15/2021	
INIMAR	4202-2	CHECKED	11/01/2021	
		P.D.		
Description:	f Microphone	APPROVED	11/01/2021	
waterproor		J.S.	11/01/2021	


This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com

Additional considerations can be found at www.dbunlimitedco.com/technical-articles.


Top View




Side View



Bottom View





Items	Specifications	Conditions				The state of the s		
Directivity	Omnidirectional							
Sensitivity	-42 ± 3	dB						
Frequency Range	50 ~ 16,000	Hz						
Rated Voltage	2	V						
Voltage Range	1 ~ 10	V		REVISION HISTORY				
Output Impedance	2,200	Ω	REV	DESCRIPTION	DATE	APPROVED		
Max. Rated Current	500	uA		Released from Engineering	11/01/2021	J.S.		
IP Rating	IP67			NOTES				
Storage Temperature	-25 ~ +70	°C		All dimensions are in mm unless otherwise noted				
Operating Temperatur	e -20 ~ +60	°C		2) All tolerances are ± 0.5 mm unless otherwise noted				
Signal to Noise Ratio	60	dB		3) All parts meet RoHS				
Mount Type	Thru Hole			4) Subject to change or redrawn without notice				
Connection Method	PC Pins							