

Ratings:
 Current 10A
 Voltage 300 V
 Wire Size 30-16AWG
 Test Voltage 1.25 kV
 Rated Torque / Screw Size 0.4Nm / M2

Rated Cross Section:
 Single Wire (solid) 1.5mm²
 Stranded Wire (flexible) 1.0mm²
 Stranded Wire with Ferrules 0.5mm²

Dimensions:
 Spacing 3.81mm
 PCB Hole Diameter 1.0^{+0.09}_{-0.06} mm
 Stripped Length 5.0mm

Materials:
 Insulating Material PA
 Flammability UL94V-0
 Temperature -30°C/+105°C
 Block CuZn
 Wire Guard CuSn
 Color Green

