

TOP VIEW



SIDE VIEW



BOTTOM VIEW



	Specifications		Notes		Revision History					
Description	Value	Unit			Version	Description		Date	Approved	
Technology	Electro-Mechanical		1) All dimensions are in mm unless otherwise noted		1	Released from Engineering			10/21/2013	J.S
Resonant Frequency	3,100	(Hz)	2) All parts meet RoHS							
Rated Voltage	1.5	(V)								
SPL @ 10cm	80	(dBA)								
Tone	Single									
Mount Type	Thru Hole									
Voltage Range	1.2 ~ 3	(V)								
Max Rated Current	25	(mA)								
Housing Material	NORYL				Drawn by	Date	Checked by	Date	Approved by	Date
Operating Temperature	-30 ~ +70	°C			A.B.	10/21/2013	C.E.	10/21/2013	J.S	10/21/2013
Storage Temperature	-40 ~ +85	°C		Electro Mechanical In	dicator	IE123101-1				
Weight	2	(g)		Electro-Mechanical Indicator		IET72T0T-T				

Additional considerations can be found at www.dbunlimitedco.com/technical-articles.