


THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO RF INDUSTRIES.
 ANY UNAUTHORIZED USE OF THIS DRAWING IS EXPRESSLY PROHIBITED
 WITHOUT WRITTEN PERMISSION FROM RF INDUSTRIES.
 ANY VIOLATION IS PUNISHABLE UNDER U.S. COPYRIGHT LAWS.

ALL DIMENSIONS ARE REFERENCE ONLY

PART NO.		RMX-8010-1B		
REV	DESCRIPTION	DWN	DATE	APPROVED
A	ENGINEERING RELEASE	CZS	11/11/97	R. RICE
B	WAS RFX-8010-1B	CZS	6/3/99	R. RICE



RECOMMENDED STRIPPING DIMENSIONS

1. CRIMPED FERRULE
HEX CRIMP SIZE .128"
2. CONTACT PIN TO SOLDER

SPECIFICATIONS:

IMPEDANCE: 50 OHMS
 FOR RG-174, 188, 188A, 316/U, ALPHA 9174, 9316,
 BELDEN 8216, 83269, 83284, 84316 & TIMES LMR-100A CABLE

1	BODY	1	BRASS	GOLD, 3 MICRO	008974
2	MCX BODY	1	BeCu	GOLD, 3 MICRO	
3	INSULATOR	1	PTFE	---	
4	PIN	1	BRASS	GOLD, 30 MICRO	
5	INSULATOR	1	DELRIN	---	
6	COVER	1	BRASS	GOLD, 3 MICRO	
7	FERRULE	1	COPPER	GOLD, 3 MICRO	
8					
9					
10					
11					
12					
13					
14					

DRAWN	C. ZUNIGA	6/3/99
CHECKED		
ORJ DRAWN	C. ZUNIGA	11/11/97

#	DESCRIPTION	QTY	MATRL	FINISH	APPROVALS	DATE
---	-------------	-----	-------	--------	-----------	------

UNLESS OTHERWISE SPECIFIED:
 1. REMOVE ALL BURRS
 2. BREAK ALL CORNERS & EDGES .005 R. MAX.
 3. CHAMFER 1ST & LAST THREADS 45°
 4. SURFACE ROUGHNESS 63 FINISH MIL-STD-10
 5. DIAMETERS ON COMMON CENTERS TO BE CONCENTRIC WITHIN .002 T.I.R.
 6. ALL DIMENSIONS ARE AFTER PLATING.

DIMENSIONS ARE IN INCHES AND [MILLIMETERS]
 UNLESS OTHERWISE NOTED TOLERANCES ARE:

DECIMALS	DIAMETER
.XXX±.003 [.08]	.XXX±.001 [.03]
.XX±.005 [.13]	.XX±.003 [.08]

RF connectors 7610 MIRAMAR RD
 SAN DIEGO, CA 92126
 (858) 549-6340
 DIVISION OF RF INDUSTRIES, LTD. (858) 549-6345 FAX

MCX CRIMP PLUG
 RIGHT ANGLE

SIZE	CABLE GROUP	DWG NO.	REV
A	B	RMX-8010-1B	B
SCALE:	NTS	CAD FILE	OUTLINE
SHEET			1 OF 1