



ELECTRONICS, INC.
 44 FARRAND STREET
 BLOOMFIELD, NJ 07003
 (973) 748-5089

NTE3031 Phototransistor Detector NPN-Si, Visible & IR

Absolute Maximum Ratings: ($T_A = +25^\circ\text{C}$ unless otherwise specified)

Collector-Emitter Voltage, V_{CEO}	30V
Emitter-Collector Voltage, V_{ECO}	5V
Continuous Device Dissipation, P_D	150mW
Derate Above 25°C	1.43mW/ $^\circ\text{C}$
Operating Junction Temperature Range, T_J	-55° to $+125^\circ\text{C}$
Storage Temperature Range, T_{stg}	-65° to $+150^\circ\text{C}$
Lead temperature (During Soldering, 3 min), T_L	$+260^\circ\text{C}$

Electrical Characteristics: ($T_A = +25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Static Characteristics						
Collector Dark Current	I_D	$V_{CE} = 10V$	-	-	100	nA
Collector-Emitter Breakdown Voltage	$V_{(BR)CEO}$	$I_C = 100\mu A$	30	-	-	V
Emitter-Collector Breakdown Voltage	$V_{(BR)ECO}$	$I_E = 100\mu A$	5	-	-	V
Saturation Voltage	$V_{CE(sat)}$	$I_C = 0.4mA$	-	0.2	-	V
Optical Characteristics						
Light Current	I_L	$V_{CE} = 5V, R_L = 100\Omega$, Note 1	1	-	-	mA
Photo Current Rise Time	t_r	$R_L = 1000\Omega, V_{CC} = 5V,$ $I_L = 1mA$ (Peak)	-	6	-	μs

Note 1. Radiation flux density (H) equal to $5mW/cm^2$ emitted from a tungsten source at a color temperature of 2875 K.

Note 2. Angular response is defined as the total included angle between the half sensitivity points and assuming a point source.

