YAMAICHI PKS019-401X-0 MICRO HDMI CONNECTORS

ELECTRONICS 19 PINS, 0.75MM PITCH, R/A STANDARD SMT MOUNT TYPE D HDMI

SPECIFICATIONS:

Insulation Resistance:

- 100MΩ min. at 500V DC (unmated)
- > 10MΩ min. at 150V DC (mated)

Withstanding Voltage:

- > 250V AC for 1min (unmated)
- > 150V AC for 1min (mated)

Voltage Rating: 40V AC Current Rating: 0.3A Contact Resistance: 100mQ max. at 20mV max. Operating Temp.: -20°C ~ +85°C Mating Cycle: 5,000 times Insertion Force: 44N Max



ഹ ; +|

S.

max 4

27

m.

Note 85

PKS019-401X-0 Series Name 19 Pins **Mounting Options:** 0 = SMT Mount 1 = T/H Mount




MATERIALS AND FINISH: · Contacts: Cu Alloy

- Metal Shell & Flange: Cu Alloy
- Insulator Body: High Performance Polyamide


FEATURES:


- Automotive Grade Type E HDMI
- HDMI ver. 1.4b compliant
- Optional Flange for additional mount security
- · NO RESTRICTIN on circuitry layout pattern area
- PKH019 HDMI Cable Assembly Available
- R/A SMT Standard Mount
- RoHS and REACH compliant

OUTLINE DIMENSIONS (MM):









6.00

5.80 ±0.15

Through Hole Mount ver.

© 2020 Yamaichi Electronics USA Incorporated. All brand or product names may be trademarks of their respective companies. Yamaichi Electronics USA Inc. Visit Us @ WWW.YEU.COM Email: Info@yeu.com TEL: 408-715-9100

DISCLAIMER: PRODUCT DATA & DIMENSIONS ARE SUBJECT TO CHANGES WITHOUT NOTICE