



SPECIFICATION CONTROL DRAWING

THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO RF INDUSTRIES, LTD. ANY UNAUTHORIZED USE OF THIS DRAWING IS EXPRESSLY PROHIBITED. ANY VIOLATION IS PUNISHABLE UNDER U.S. COPYRIGHT LAWS.

REV	DESCRIPTION	DWN	DATE	APPROVED
A1	ENGINEERING RELEASE	KMM	6/14/93	J. BENZ
B	ENGINEERING RELEASE	KMM	11/7/95	R. RICE
C	ADD NOTE TO CONTACT ITEM #2 / CHG FORMAT	CZS	10/28/97	R. RICE
D	CHANGE BODY ID / REMOVE P/N / LOOSEN TOLERANCES	CZS	8/9/99	R. RICE

000000

ALL DIMENSIONS ARE REFERENCE ONLY



SUGGESTED MOUNTING CONFIGURATION

SPECIFICATIONS:

IMPEDANCE: 50 OHMS
 WORKING VOLTAGE: 500 VRMS @ SEA LEVEL
 FREQUENCY RANGE: 0-7 GHz
 INTERFACE PER MIL-STD-348, SECTION 313.2

DIMENSIONS ARE IN INCHES AND [MILLIMETERS]

UNLESS OTHERWISE NOTED TOLERANCES ARE:
 DECIMALS DIAMETER

RFconnectors

DIVISION OF RF INDUSTRIES, LTD.

7610 MIRAMAR RD
 SAN DIEGO, CA 92126
 (858) 549-6340
 (858) 549-6345 FAX

RFT-1211-1

TNC FEMALE BULKHEAD, FRONT MOUNT

ITEM	DESCRIPTION	QTY	MATERIAL	FINISH
6	HEX NUT	1	BRASS	NICKEL
5	LOCKING SOLDER LUG	1	BRASS	NICKEL
4	PRESS FIT WASHER	1	BRASS	NICKEL
3	DIELECTRIC	1	PTFE	NONE
2	CONTACT	1	BRASS	GOLD
1	BODY	1	BRASS	NICKEL

DRAWN	C. ZUNIGA	8/9/99
CHECKED		
ORJ DRAWN	D. FRIAS	11/24/87
APPROVALS		DATE

SIZE	CABLE GROUP	DWG NO.	REV
A	N/A	8140	D
SCALE:	2:1	CAD FILE	13ARC B
			SHEET 1 OF 1