

RSL1PRBU

Harmony, Slim interface relay pre-assembled, 6 A, 1 CO, with LED, with protection circuit, spring terminals, 24 V AC/DC



Main

Range of Product	Harmony Electromechanical Relays
Series name	Interface relay
Product or Component Type	Pre-assembled plug-in relay with socket
Device short name	RSL
Contacts type and composition	1 C/O
Contact operation	Standard
[Uc] control circuit voltage	24 V DC
[Ithe] conventional enclosed thermal current	6 A -40...131 °F (-40...55 °C)
Status LED	With
Shape of pin	Flat (PCB type)

Complementary

Fixing Mode	Plastic compression spring
Average resistance	3390 Ohm DC 23 °C +/- 10 %
[Ui] rated insulation voltage	250 V EN/IEC 277 V cUL
[Uimp] rated impulse withstand voltage	6 kV IEC
Contacts material	Silver alloy (AgSnO2)
[Ie] rated operational current	6 A 1 C/O AC-1/DC-1)IEC/UL
Minimum switching current	100 mA
Maximum switching voltage	277 V
Switching voltage	12 V
Maximum switching capacity	1500 VA 150 W
Minimum switching capacity	120 mW
Operating rate	<= 72000 cycles/hour no-load <= 360 cycles/hour under load
Mechanical durability	10000000 cycles
Electrical durability	60000 cycles resistive, 6 A 250 V, AC-1
Operating time	5 ms reset 12 ms
Marking	CE
Protection category	RT III
Test levels	Level A
Operating position	Any position
Height	3.09 in (78.6 mm)
Width	0.24 in (6.2 mm)
Depth	3.98 in (101 mm)
Terminals description ISO n°1	(A1-A2)CO (11-12-14)OC
Sale per indivisible quantity	10
Net Weight	0.06 lb(US) (0.029 kg)
Load current	6 A 250 V AC 0.5 mm mounting distance
Average coil consumption	0.17 W, DC

Drop-out voltage threshold	>= 0.05 Uc
Contact terminal arrangement	Separate
Connections - terminals	Spring terminals, 1 x 0.2...1 x 1.5 mm ² AWG 24...AWG 16) flexible with cable end Spring terminals, 1 x 0.2...1 x 1.5 mm ² AWG 24...AWG 16) solid without cable end
Safety reliability data	B10d = 60000
Clamping force	10...40 N
Control Type	Without push-button
Mounting Support	35 mm symmetrical DIN rail
Device presentation	Complete product

Environment

Input voltage	24 V AC/DC 21.6...28.8 V)
Dielectric strength	1000 V AC between contacts 4000 V AC between coil and contact
Standards	EN/IEC 61810-1 CSA C22.2 No 14 UL 508
Product Certifications	UL CSA GOST
Ambient Air Temperature for Storage	-40...185 °F (-40...85 °C)
Vibration resistance	10 gn +/- 1 mm 10...150 Hz)10 cycles not operating EN/IEC 60068-2-6 5 gn +/- 1 mm 10...150 Hz)10 cycles in operation EN/IEC 60068-2-6
IP degree of protection	IP40 conforming to EN/IEC 60529
Shock resistance	10 gn 11 ms) in operation EN/IEC 60068-2-27 5 gn 11 ms) not operating EN/IEC 60068-2-27
Ambient air temperature for operation	-40...131 °F (-40...55 °C)

Ordering and shipping details

Category	21127 - ZELIO ICE CUBE RELAYS
Discount Schedule	CP2
GTIN	3606480077906
Nbr. of units in pkg.	1
Package weight(Lbs)	0.99 oz (28 g)
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.24 in (0.6 cm)
Package 1 width	3.15 in (8 cm)
Package 1 Length	4.06 in (10.3 cm)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	10.97 oz (311 g)
Package 2 Height	3.35 in (8.5 cm)
Package 2 width	2.80 in (7.1 cm)
Package 2 Length	4.21 in (10.7 cm)
Unit Type of Package 3	S03
Number of Units in Package 3	300
Package 3 Weight	23.86 lb(US) (10.823 kg)
Package 3 Height	11.81 in (30 cm)
Package 3 width	11.81 in (30 cm)
Package 3 Length	15.75 in (40 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------

Dimensions

