



SIGN	DATE	DESCRIPTION	APPROVER
△	09/01'10	Current rating is changed from 20A to 15A	Aaron
△	09/01'10	Add cULus	Aaron
△	02/12'14	Update the drawing	Aaron

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

- Material**
- Item (a) Terminal screw: Steel Zinc plating "-" slot type
 - Item (b) Clamp: Brass (CuZn), Ni plating
 - Item (c) Wire guard solder pin: Brass, Tin plated
 - Item (d) Terminal housing: Thermoplastic (UL94V-0)

- Electrical**
- Voltage rating: 300VAC
 - △ ● Current rating: 15A
 - Wire range:
 - Solid wire (AWG): 12-28
 - Stranded wire (AWG): 12-28
 - Torque (Lb-In): 4.3
 - Screw: M3
 - Wire strip length: 6-7mm
 - Withstanding Voltage: 1.6KV
 - Operating temperature: -40°C to +115°C
 - △ ● Soldering temperature: 260°C±5°C/5 Sec
 - △ ● Safety Approval: cULus
 - Critical dimension:

PART NO.

YH xx 21 x 1 xxxx G

RoHS compliant (lead<4%) In copper Alloy

No. of poles	0 Black (RAL9005)	0000 Standard @ Logo
06 3x2P POLES	5 Green (RAL6018/T)	000A Standard ANY Logo
09 3x3P POLES	6 Blue (RAL5015/A)	Any special item by customer request,
	8 Grey (RAL7035/D)	please contact sales department.
72 3x24P POLES	C Green (RAL6018/U)	

DIMENSION

Dim A	N/3x5.08
Dim B	(N/3-1)x5.08

N=Number of poles

Poles	Dim A	Dim B
3x2pole~3x6pole	±0.15	±0.15
3x7pole~3x12pole	±0.25	±0.25
3x13pole~3x18pole	±0.35	±0.35
3x19pole~3x24pole	±0.40	±0.40

ANYTEK		CUSTOMER COPY	
ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD			
TITLE	YH 5.08mm Series 3x2P-3x24P (Without Cover)		
PART NO.	YHxx21x1xxxxG	DWG NO.	8YH0001
APPROVED	CHECKED	DESIGNED	DRAWN
		Guoxue 2014.02.12	Guoxue 2014.02.12
SHEET: 01/01		UNIT: mm	Tolerance
REV.: E		SCALE: NONE	X. ±0.50
			X.X ±0.30
			X.XX ±0.10
			X° ±1°