



Main

Product or Component Type	Controllers separate parts
Accessory / separate part category	Control accessories
Product Specific Application	Light hoisting applications
Product Compatibility	XKB
Accessory / Separate Part Type	Potentiometer
Condition of use	For applications requiring an extended neutral zone
Ohmic value	4700 Ohm
Size	15 mm

Complementary

Standards	UTE 93-265
Potentiometer characteristic	Linear function Continuous rotational operation
Operating angle	360 °
Mechanical durability	3000000 cycles
Centre tap	Wired out to terminal
Centre tap dead zone	40 °
Power dissipation in W	3 W 185 °F (85 °C)
Connections - Terminals	Flying leads from soldered standard tags
Net Weight	0.12 lb(US) (0.055 kg)

Environment

Mounting Mode	By the body
---------------	-------------

Ordering and shipping details

Category	22474-PUSHBUTTON,CRANE JOYSTICKS
Discount Schedule	I
GTIN	3389110147148
Nbr. of units in pkg.	1
Package weight(Lbs)	2.22 oz (63.0 g)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.77 in (4.5 cm)
Package 1 width	2.28 in (5.8 cm)
Package 1 Length	2.48 in (6.3 cm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------