





REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	INITIAL RELEASE.	2013.03.27	邱明周



Specifications
 Current Rating: 2.0Amp
 Insulation Resistance: 1000MΩMin.
 Dielectric Withstanding Voltage: 500VAC
 Contact Resistance: 20mΩMax.
 Operating Temperature: -40°C to +105°C
 Materials
 Contact Material: Phosphor Bronze
 Insulator Material: High Temperature Thermoplastic, UL 94V-0 Nylon 6T(無鹵) or the equivalent material
 All materials must meet Greenconn requirement for environment protection.

Recommended P.C.Board Layout
 (Tolerance: ±0.05)



Ordering Information

C SFB207 - XX XX A 001 R 1 A X

No. of Pins per Row 02~40
 Standard Plating 02=Gold Flash
 Selective Plating 01=Tin 05=Gold Flash/Tin
 Color 1=Black
 Standard Packing A=Box
 Selective Packing C=Tube

格菱股份有限公司
Greenconn Corporation

GENERAL TOLERANCE	
X.*±5.0°	X.±0.30
.X*±3.0°	.X±0.25
.XX*±2.0°	.XX±0.15
.XXX*±1.0°	.XXX±0.10

DESIGN: 邱明周	DATE: 2013.03.27
CHECKED: 劉北平	DATE: 2013.03.27
AUDITED: 林萬輝	DATE: 2013.03.27
APPROVED: 李輝	DATE: 2013.03.27

DWG. NO.	CSFB207-CA1RA
PART NO.	CSFB207-XXXX A001R1AX

TITLE.	2.00 FEMALE HEADER DUAL ROWS R/A TYPE CONNECTOR
--------	---

REV.	UNIT.	SCALE.	PAGE.
01	mm	4:1	1/1