



■ 技术参数 SPECIFICATIONS:

- ◆ 线数: 2~16
- ◆ 适用线规: AWG #32~#26
- ◆ 适用导线: AWG #32~#26
- ◆ 额定电压: 125V DC/AC
- ◆ Vol tage Rating: 125V DC/AC
- ◆ 额定电流: 1.0A
- ◆ Current Rating: 1.0A
- ◆ 耐压: 500V AC
- ◆ Withstand Vol tage: 500V AC
- ◆ 温度范围: -25° C~+85° C
- ◆ Working Temperature: -25° C~+85° C
- ◆ 绝缘电阻:  $\geq 500M\Omega$
- ◆ Insulation Resistance: 500M $\Omega$  (MIN)
- ◆ 接触电阻:  $\leq 20m\Omega$
- ◆ Contact Resistance: 20m $\Omega$  (MAX)
- ◆ 材质/颜色: 尼龙66 黑, 94V-0本色
- ◆ Material: Nylon66 Ul 94V-0 Color Nature
- ◆ 包装数量: pcs
- ◆ Packaging Quantity: pcs

序号	尺寸			序号	尺寸		
Circuitso	Dim.A	Dim.B	Dim.C	Circuitso	Dim.A	Dim.B	Dim.C
2	1.50	3.40	4.50	10	13.50	15.40	16.50
3	3.00	4.90	6.00	11	15.00	16.90	18.00
4	4.50	6.40	7.50	12	16.50	18.40	19.50
5	6.00	7.90	9.00	13	18.00	19.90	21.00
6	7.50	9.40	10.50	14	19.50	21.40	22.50
7	9.00	10.90	12.00	15	21.00	22.90	24.00
8	10.50	12.40	13.50	16	22.50	24.40	25.50
9	12.00	13.90	15.00				

APPROVALS		DATE	DRAWING NO.	
DRAWN	G.M.Chen	2015/5/22	ELECTRONICS CO.,LTD	
CHECKED			TITLE: 1.5mm Crimp Style Connectors	
APPROVALS			PART NO.	A1501-XXP
TOLERANCES ARE		ANGLE	UNIT:	SCALE: 1:1
10~30	±0.20	±2°	mm	SHEET 1 OF 1
3~10	±0.15			PROJ.
~ 5	±0.10			

  

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			