



技术参数:

线数 (Poles) : 2~12
 适用线规 (Applicable wires) : AWG22#~18#
 温度范围 (Temperature range) : -25°C~85°C
 额定电压 (Voltage rating) : 250V.Ac/Dc
 额定电流 (Current rating) : 7.5A
 接触电阻 (Contact resistance) : $\leq 0.02\Omega$
 绝缘电阻 (Insulation resistance) : $\geq 1000M\Omega$
 耐压 (Withstand voltage) : 1500V.Ac/1min
 材料 (Material) : (Nylon) 66 UL94V-2(0)
 孔座 (Housing)

Circuits	Dim.A	Dim.B
2	3.96	7.92
3	7.92	11.88
4	11.88	15.84
5	15.84	19.8
6	19.8	23.76
7	23.76	27.72
8	27.72	31.68
9	31.68	35.64
10	35.64	39.6
11	39.6	43.56
12	43.56	47.52

APPROVALS		DATE	PART NO.		SCALE	SHEET
DRAWN	G.M.Chen	2015/5/4	A3960-XXP		1:1	1 OF 1
CHECKED			A3960-XXP			
APPROVALS			A3960-XXP			
TITLE: 3.96mm Crimp Style Connectors ELECTRONICS CO.,LTD 德之隆®						
TOLERANCES ARE 30~40H ±0.30 ANGLE 10~30 ±0.20 5~10 ±0.15 ±2° DRAWING NO.						
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			