



技术参数 SPECIFICATIONS:

- ◆ 线数: 2~16
- ◆ Poles: 2~16
- ◆ 适用线规: AWG #28~#32
- ◆ Applicable Wire: AWG #28~#32
- ◆ 额定电压: 50V DC/AC
- ◆ Voltage Rating: 50V DC/AC
- ◆ 额定电流: 1.0A
- ◆ Current Rating: 1.0A
- ◆ 耐压: 500V AC
- ◆ Withstand Voltage: 500V AC
- ◆ 温度范围: -25°C~+85°C
- ◆ Working Temperature: -25°C~+85°C
- ◆ 绝缘电阻: ≥100MΩ
- ◆ Insulation Resistance: 100MΩ(MIN)
- ◆ 接触电阻: ≤20mΩ
- ◆ Contact Resistance: 20mΩ(MAX)
- ◆ 材质/颜色: 尼龙94V-0本色
- ◆ Material: Nylon 66 UL 94V-0 Color Nature
- ◆ 包装数量: 1000 pcs
- ◆ Packaging Quantity: 1000 pcs

序号 Circuits	尺寸		序号 Circuits	尺寸	
	Dim.A	Dim.B		Dim.A	Dim.B
2	1.00	3.00	10	9.00	11.00
3	2.00	4.00	11	10.00	12.00
4	3.00	5.00	12	11.00	13.00
5	4.00	6.00	13	12.00	14.00
6	5.00	7.00	14	13.00	15.00
7	6.00	8.00	15	14.00	16.00
8	7.00	9.00	16	15.00	17.00
9	8.00	10.00			

APPROVALS		DATE	PART NO.		SCALE	SHEET
DRAWN	G.M.Chen	2015/5/22	A1001-XXP		1:1	1 OF 1
CHECKED						
APPROVALS						
TITLE: 1.00mm Crimp Style Connectors						
ELECTRONICS CO.,LTD						
DEALON 德之隆®						
TOLERANCES ARE						
	30~80L	±0.30	ANGLE			
	10~30	±0.20				
	5~10	±0.15	±2°			
	~5	±0.10				
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			