





版本	变更内容	工程确认	日期



SPECIFICATIONS

- 1、Current Rating: 1A AC, DC
- 2、Voltage Rating: 125V AC, DC
- 3、Temperature Range: -25°C~+85°C
- 4、Contact Resistance: 20MΩ Max
- 5、Insulation Resistance: 100MΩ Min
- 6、Withstanding Voltang: 500V AC/minute
- 7、Material: Wafer LCP、UL94V-0
PIN Brass Tin-plated
Solder tad Brass Tin-plated



编号	尺寸 (mm)	
	A	B
YTC-A1251-02AB	1.25	7.35
YTC-A1251-07AB	7.50	13.60
YTC-A1251-08AB	8.75	14.85
YTC-A1251-09AB	10.00	16.10
YTC-A1251-10AB	11.25	17.35
YTC-A1251-11AB	12.50	18.60
YTC-A1251-12AB	13.75	19.85
YTC-A1251-13AB	15.00	21.10
YTC-A1251-14AB	16.25	22.35
YTC-A1251-15AB	17.50	23.60
YTC-A1251-16AB	18.75	24.85
YTC-A1251-20AB	23.75	29.85

技术要求:

1. “ ”表示为重要尺寸:
A塑料为开口结构 8P以上外形尺寸2.30±0.25

深圳市怡远科技有限公司 SHENZHEN YIYUAN TECHNOLOGY CO., LTD		页码 (SHEET)	1/1	单位(UNIT): MM
		版本 (REV)	A1	比例(SCALE)
品名 (ITEM NO)	1.25间距开口立贴 WAFER DIP TYPE	日期 (DATE)	2021. 10. 12	
料号 (PART NO)	YTC-A1251-**-AB	设计 (DESIGN)	LUO	
图号 (DWG NO)		审核 (CHECKED)	ROGER LI	GENERAL TOLERANCE X.±0.25 X'.±2" .XX±0.20 .XX'±1" .XXX±0.15 .XXX'±0.5" .XXX±0.10 .XXX'±0.5"
		核准 (APPROVED)	ROC ZHAO	

These drawings and specifications are Shenzhen Yiyuan Technology Co Ltd.The property should not be copied. Without Shenzhen Yiyuan Technology Co. Ltd.Prior written consent to copy or use in any way. Email at info@yiyuanswitches.com