







CATEGORY	DESCRIPTION	P/N #
CONNECTOR	RJ45 5224系列 1x4 180度直插全塑无灯(通用)	MJ522488-XX14-HXPDN2

REV.	ECN NO	DESCRIPTION	REVISED	DATE
A01		New Release	YST	2020.05.09
A02		整理图面	YST	2021.03.02



- 1.RJ ELECTRICAL CHARACTERISTICS
- 1-1: VOLTAGE:125V AC RMS
  - 1-2: CURRENT RATING:1.5A
  - 1-3: CONTACT RESISTANCE: 40mΩ MAX.
  - 1-4: INSULATION RESISTANCE: 500MΩ MIN.
  - 1-5: DIELECTRIC WITHSTANG VOLTAGE :1000V AC
  - 1-6: OPERATURE TEMPERATURE: -40°C~80°C

MJ522488-XX14-HXPDN2

TABLE1

X   HOUSING
B   BLACK
Y   YELLOW(123C)

TABLE3

X   MATERIAL
P   PBT
8   PART

TABLE2

X   TERMINAL PLATING
0   G/F PLATING
1   AU 3U" PLATING
2   AU 6U" PLATING
3   AU 15U" PLATING
4   AU 30U" PLATING

C	INSERT	4	THERMOPLASTIC UL94V-0	SEE TABLE
b	TERMINAL	32	PHOSPHOR BRONZE Ø0.46mm	SEE TABLE2
a	HOUSING	1	THERMOPLASTIC UL94V-0	SEE TABLE
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR

UNLESS OTHERWISE SPECIFIED TOLERANCES

DECIMALS: ANGLES:

X : ±0.5 X : ±2°

X.X : ±0.3 X.X : ±1'

X.XX : ±0.2 X.XX : ±0.2

PC Board Layout Component Side Shown

SCALE: 1/1 UNIT: mm

SIZE: A3 PAGE: 1 OF 1 REV: A02

APPROVED BY: XSY

CHECKED BY: XSY

DWG. NO.:

PREPARED BY: YST



东莞市合陵电子有限公司  
DongGuan Heling Electronic Co., LTD

CUSTOMER COPY