


CATEGORY	DESCRIPTION	P/N #
CONNECTOR	RJ45 8P8C 全塑1X2	MJ5388-XX12-HRN1




REV.	ECN NO	DESCRIPTION	REVISED	DATE
A01	—	New Release	XSY	2017.04.20
A02	—	新增主体颜色选项	ZSH	2020.08.26





X	Housing Color	X Terminal Plating
B	Black	0 G/F Plating
U	Blue	1 Au 3u" Plating
Y	Yellow 115C	2 Au 6u" Plating
G	Gray 7544C	3 Au 15u" Plating
G1	Gray D113C	

MJ5388-XX12-HRN1

- SPECIFICATION
- VOLTAGE RATING: 150 VAC RMS.
  - CURRENT RATING: 1.5 AMP
  - CONTACT RESISTANCE: 40 mΩ MAX
  - INSULATION RESISTANCE: 500MΩ MIN.
  - WITHSTAND VOLTAGE: AC1000V RMS 60s.
  - OPERATING TEMPERATURE: -40°C~+80°C



Recommend PCB Layout  
(Jack Top View)  
Tolerance: ±0.05mm  
PCB Thickness: 1.6mm



VIEW A  
SCALE 2:1

b	TERMINAL	16	PHOSPHOR BRONZE	Ø0.46mm	G/F	
d	HOUSING	1	PBT UL94V-0		SEE TABLE 1	
NO.	PART NAME	QTY	MATERIAL		PLATING & COLOR	Remark

UNLESS OTHERWISE SPECIFIED TOLERANCES

DECIMALS:	ANGLES:
X : ±0.5	X : ±2°
XX : ±0.3	XX : ±1°
XXX : ±0.2	

SCALE: 1/1	UNIT: mm	DWG. NO:
SIZE: A3	PAGE: 1 OF 1	REV: A02
APPROVED BY	CHECKED BY	PREPARED BY
DICK	XSY	XSY

**东莞市合陵电子有限公司**  
DongGuan Heling Electronic Co.,LTD

CUSTOMER COPY