





CATEGORY	DESCRIPTION	P/N #
CONNECTOR	RJ45 8P8C 全塑1X4	MJ5388-Y014-HRN1S




REV.	ECN NO	DESCRIPTION	REVISED	DATE
A01	—	New Release	XSY	2017.12.02
A02	ENG181106001	更改脚柱尺寸	XSY	2018.11.06



- SPECIFICATION**
- VOLTAGE RATING: 125 VAC RMS.
 - CURRENT RATING: 1.5 AMP
 - CONTACT RESISTANCE: 40 mΩ MAX
 - INSULATION RESISTANCE: 500MΩ MIN.
 - WITHSTAND VOLTAGE: AC500V RMS 60s.
 - OPERATING TEMPERATURE: -40°C~+80°C



Recommend PCB Layout
(Jack Top View)
Tolerance: ±0.05mm
Recommend PCB Thickness: 1.6mm



东莞市合陵电子有限公司
DongGuan Heling Electronic Co.,LTD
Connector

UNLESS OTHERWISE SPECIFIED TOLERANCES	SCALE:1/1	UNIT: mm	DWG.NO:
SIZE: A3	PAGE:1 OF 1	REV:A02	

b	TERMINAL	32	PHOSPHOR BRONZE	∅0.46mm	G/F	
d	HOUSING	1	PBT UL94V-0		Yellow	115C
NO.	PART NAME	Q'TY	MATERIAL		PLATING & COLOR	Remark

DECIMALS:	ANGLES:	APPROVED BY	CHECKED BY	PREPARED BY
X :±0.5	X :±2°	DICK	XSY	XSY
XX :±0.3	XX :±1°	CUSTOMER COPY		
XXX :±0.2				