



CATEGORY	DESCRIPTION	P/N #
CONNECTOR	RJ45 8P8C 全塑无灯	MJ5688-XX11-RN1

REV.	ECN NO	DESCRIPTION	REVISED	DATE
A04		新增颜色选项	XSY	2018.03.02
A05		新增灰色选项	XSY	2018.12.18
A06		新增红色选项	YST	2019.11.22
A07		新增颜色号	LXY	2020.09.05



- SPECIFICATION**
- VOLTAGE RATING: 150 VAC RMS.
  - CURRENT RATING: 1.5 AMP
  - CONTACT RESISTANCE: 40 mΩ MAX
  - INSULATION RESISTANCE: 500MΩ MIN.
  - WITHSTAND VOLTAGE: AC1000V RMS 60s.
  - OPERATING TEMPERATURE: -40°C~+85°C





Table 1

X	Terminal Plating
0	Au G/F" Plating
1	Au 3U" Plating
2	Au 6U" Plating
3	Au 15U" Plating

Table 2

X	Housing Color	Housing Material
B	Black	PBT UL94V-0
U	Blue 7691C/A07	PBT UL94V-0
Y	Yellow	
W	White	
G	GRAY	
R	RED	
1	Black	
2	Blue	PA9T UL94V-0
3	Yellow	
4	White	

Recommend PCB Layout  
(Jack Top View)  
Tolerance: ±0.05mm  
Recommend PCB Thickness: 1.6mm

**東莞市合陵電子有限公司**  
DongGuan Heling Electronic Co.,LTD

UNLESS OTHERWISE SPECIFIED TOLERANCES	SCALE: 1/1	UNIT: mm	DWG.NO:
DECIMALS: X :±0.5	SIZE: A3	PAGE: 1 OF 1	REV: A07
ANGLES: X : ±2°	APPROVED BY	CHECKED BY	PREPARED BY
X.X : ±0.3	DICK	XSY	LXY
X.XX : ±0.2	CUSTOMER COPY		

b	TERMINAL	8	PHOSPHOR BRONZE	∅0.46mm	See Table 2	
a	HOUSING	1	See Table 1		See Table 1	
NO.	PART NAME	QTY	MATERIAL		PLATING & COLOR	Remark