







CATEGORY	DESCRIPTION	P/N #
CONNECTOR	RJ45 8P8C 帶壳沉板H=6.0mm	MJ88-BX11-HRV6

REV.	ECN NO	DESCRIPTION	REVISED	DATE
A01	—	New Release	XSY	2014.02.13



X	Terminal Plating
0	G/F Plating
1	Au 3u" Plating
2	Au 6u" Plating
3	Au 15u" Plating
4	Au 30u" Plating


Part No.:
MJ88-BX11-HRV6

Recommend PCB Layout
(Jack Top View)
Tolerance: ±0.05mm
Recommend PCB Thickness: 1.2mm

- SPECIFICATION
- VOLTAGE RATING: 150 VAC RMS.
 - CURRENT RATING: 1.5 AMP
 - CONTACT RESISTANCE: 40 mΩ MAX
 - INSULATION RESISTANCE: 500MΩ MIN.
 - WITHSTAND VOLTAGE: AC1000V RMS 50Hz or 60Hz MIN.
 - OPERATING TEMPERATURE: -40°C~+80°C

c	SHELL	1	BRASS T=0.2mm	Ni PALTING	
b	TERMINAL	8	PHOSPHOR BRONZE T=0.3mm	Au PALTING	
a	HOUSING	1	LCP UL94V-0	BLACK	
NO.	PART NAME	QTY	MATERIAL	PLATING & COLOR	Remark

UNLESS OTHERWISE SPECIFIED TOLERANCES		SCALE: 1/1		UNIT: mm	DWG.NO:
DECIMALS:	ANGLES:	SIZE: A3	PAGE: 1 OF 1	REV: A01	WI-061-115
X : ±0.5	X : ±2°	APPROVED BY	CHECKED BY	PREPARED BY	
XX : ±0.3	XX : ±1°	Dick	XSY	XSY	
XXX : ±0.2		CUSTOMER COPY			


东莞市合陵电子有限公司
Dongguan Heling Electronic Co., LTD
 Connector