




CATEGORY	DESCRIPTION	P/N #
CONNECTOR	RJ45 8P8C 帶壳沉板H=6.0mm(帶燈)	MU88-BX11-HRV LX6




REV.	ECN NO	DESCRIPTION	REVISED	DATE
A02		增加灯选项	YST	2019.04.27
A03		增加灯选项	YST	2020.07.20




Part No.:
MU88-BX11-HRV LX6

X	Terminal Plating
0	G/F Plating
1	Au 3u" Plating
2	Au 6u" Plating
3	Au 15u" Plating
4	Au 30u" Plating

TABLE1		
X	LED-L (清面灯)	LED-R (清面灯)
1	GREEN (清面灯)	YELLOW (清面灯)
2	YELLOW (清面灯)	GREEN (清面灯)
G	YELLOW (清面灯)	Y/G (清面灯)
A	GREEN (清面灯)	G/O (清面灯)



- SPECIFICATION
- VOLTAGE RATING: 150 VAC RMS.
 - CURRENT RATING: 1.5 AMP
 - CONTACT RESISTANCE: 40 mΩ MAX
 - INSULATION RESISTANCE: 500MΩ MIN.
 - WITHSTAND VOLTAGE: AC1000V RMS 50Hz or 60Hz MIN.
 - OPERATING TEMPERATURE: -40°C~+80°C



Recommend PCB Layout
(lack Top View)
Tolerance: ±0.05mm
Recommend PCB Thickness: 1.2mm

A	e	LED-R	1	SEE TABLE1		
	d	LED-L	1	SEE TABLE1		
	c	SHELL	1	BRASS T=0.2mm	Ni PATING	
	b	TERMINAL	8	PHOSPHOR BRONZE T=0.3mm	Au PATING	
	a	HOUSING	1	LCP UL94V-0	BLACK	
	NO.	PART NAME	QTY	MATERIAL	PLATING & COLOR	Remark

UNLESS OTHERWISE SPECIFIED TOLERANCES	DECIMALS:	ANGLES:
	X : ±0.5	X : ±2°
	XX : ±0.3	XX : ±1°
	XXX : ±0.2	

東莞市合陵電子有限公司
 DongGuan Heling Electronic Co.,LTD
 Connector
 SCALE:1/1 UNIT: mm
 SIZE: A3 PAGE:1 OF 1 REV:A03
 APPROVED BY: _____ CHECKED BY: _____ PREPARED BY: _____
 DICK: XSY
 CUSTOMER COPY