





CATEGORY	DESCRIPTION	P/N #
CONNECTOR	Modular Jack, 8P8C, 27.5	MJ88-BX11-HRVS8-X

REV.	ECN NO	DESCRIPTION	REVISED	DATE
A01	—	New Release	XSY	2015.01.16
A02	—	增加包装方式	YST	2018.10.19



Recommend PCB Layout  
(Jack Top View)  
Tolerance:  $\pm 0.05\text{mm}$

- NOTE:
1. Voltage: 150V AC RMS
  2. Current Rating: 1.5A
  3. Contact Resistance: 40mΩ MAX.
  4. Insulation Resistance: 500MΩ MIN.
  5. Dielectric Withstand Voltage: 1000V AC
  6. Operate Temperature: -40°C~80°C
  7. Durability: 750 Mating Cycles MIN.

Material & Plating

X	Terminal Plating
0	Au 1u" Plating
1	Au 3u" Plating
2	Au 6u" Plating
3	Au 15u" Plating

X	包装方式
C	卷带包装
P	吸塑盒包装

Part No.:  
MJ88-BX11-HRVS8-X



**东莞市合陵电子有限公司**  
 DongGuan Heling Electronic Co.,LTD

c	Shielding	1	Brass T=0.2mm	Ni Plating		
b	Terminal	8	Phosphor Bronze T=0.3mm	Au/Tin Plating		
a	Housing	1	LCP UL94V-0	Black		
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR	Remark	

UNLESS OTHERWISE SPECIFIED TOLERANCES		SCALE: 1/1	UNIT: mm	DWG. NO:
DECIMALS:	: ±0.5	SIZE: A3	PAGE: 1 OF 1	REV: A02
ANGLES:	: ±2°	APPROVED BY	CHECKED BY	PREPARED BY
X.XX	: ±0.3	DICK	XSY	XSY
X.XXX	: ±0.2	CUSTOMER COPY		

A

3

2

1