



CATEGORY	DESCRIPTION	P/N #
CONNECTOR	RJ45 180度SMT全塑	MJ882-BX11-H9PSN1-X

由原料号 MJ88-BX11-JPST  
变更为 MJ882-BX11-H9PSN1-X


REV.	ECN NO	DESCRIPTION	REVISED	DATE
A01	—	整理图面	XSY	2015.09.15
A02	—	区分包装方式	XSY	2018.01.17




MJ882-BX11-H9PSN1-X

X	Terminal Plating
0	Au 1u" Plating
1	Au 3u" Plating
2	Au 6u" Plating
3	Au 15u" Plating
4	Au 30u" Plating

X	包装方式
C	卷带包装
P	吸塑盒包装



Recommend PCB Layout  
(Jack Top View)  
Tolerance: ±0.05mm



ME	1	BRASS T=0.35mm	Tin PLATING
TERMINAL	8	PHOSPHOR BRONZE T=0.35mm	Au/Tin PLATING
INSERT	1	LCP UL94V-0	BLACK
HOUSING	1	PA9T UL94V-0	BLACK
PART NAME	QTY	MATERIAL	PLATING & COLOR
			Remark

UNLESS OTHERWISE SPECIFIED TOLERANCES

DECIMALS:	ANGLES:
X : ±0.5	X : ±2°
X.X : ±0.3	X.X : ±1°
X.XX : ±0.2	

**东莞市合陵电子有限公司**  
 Dongguan Heling Electronic Co., LTD  
 Connector

SCALE: 1/1	UNIT: mm	DWG. NO:
SIZE: A3	PAGE: 1 OF 1	WJ-061-151
APPROVED BY	CHECKED BY	PREPARED BY
DICK	XSY	XSY
CUSTOMER COPY		