



CATEGORY	CONNECTOR	DESCRIPTION	R45 双网口180度转接头支架1*2	P/N #	MJ88Z-BX12-HPMD1	REV.	A01	ECN NO	—	DESCRIPTION	New Release	REVISED	YST	DATE	2020.01.09
----------	-----------	-------------	---------------------	-------	------------------	------	-----	--------	---	-------------	-------------	---------	-----	------	------------



- SPECIFICATION
- VOLTAGE RATING: 125 VAC RMS.
  - CURRENT RATING: 1.5 AMP
  - CONTACT RESISTANCE: 50 mΩ MAX
  - INSULATION RESISTANCE: 500MΩ MIN.
  - WITHSTAND VOLTAGE: AC1000V RMS 50Hz or 60Hz MIN.
  - OPERATING TEMPERATURE: -40°C~+80°C

MJ88Z-BX12-HPMD1

X	Terminal Plating
0	Au 1" Plating
1	Au 3u" Plating
2	Au 6u" Plating
3	Au 15u" Plating
4	Au 30u" Plating


**东莞市合陵电子有限公司**  
 Dongguan Heling Electronic Co.,LTD

UNLESS OTHERWISE SPECIFIED TOLERANCES

SCALE: 1/1 UNIT: mm DWG.NO:

SIZE: A3 PAGE: 1 OF 1 REV: A01

b	TERMINAL	1	PHOSPHOR BRONZE T=0.35mm	Au PLATING	
a	HOUSING	2	PBT UL94V-0	BLACK	
NO.	PART NAME	QTY	MATERIAL	PLATING & COLOR	Remark

DECIMALS:	ANGLES:	APPROVED BY	CHECKED BY	PREPARED BY
X : ±0.5	X : ±2°	DICK	XSY	YST
XX : ±0.3	XX : ±1°	CUSTOMER COPY		
XXX : ±0.2				