




CATEGORY	DESCRIPTION	P/N #
CONNECTOR	RJ45 方形直通式双网卡转接头 (CAT. 5E)	MJ88Z1-BX11-HPPDX-X

REV.	ECN NO	DESCRIPTION	REVISED	DATE
A01		New Release	YST	2021.10.13
A02		增加弹片高度尺寸标注	YSH	2022.05.28



X	Terminal Plating
0	Au 1" Plating
1	Au 3u" Plating
2	Au 6u" Plating
3	Au 15u" Plating
4	Au 30u" Plating

0	有CAT. 5E, 有合陵商标L0G0
2	有CAT. 5E, 无客户商标L0G0
3	无CAT. 5E, 无客户商标L0G0
4	无CAT. 5E, 有客户商标L0G0

X	包装方式
P	吸塑包装

SPECIFICATION

- VOLTAGE RATING: 150 V Max.
- CURRENT RATING: 1.5 A Max.
- CONTACT RESISTANCE: 60 mΩ Max.
- INSULATION RESISTANCE: 500MΩ Min.
- DIELECTRIC WITHSTANDING VOLTAGE: 500 V AC FOR 1 MINUTE
- OPERATING TEMPERATURE: -40°C~+85°C

- 备注:**
- 表面要求:
光滑不刮手, 不可有披锋, 毛刺等现象, 端子不可有发白脏污等不良。
 - 带"*"为重点管控尺寸; 标识"CPK"为CPK管控尺寸。
 - 产口符合ROHS2.0标准。
 - 特殊工艺要求:
符合FCC标准规范; 采用未压接水晶头, 配合无抛PIN靠PIN, 允许轻微变形, 不允许挂到塑胶内壁不回弹。
 - 特殊测试要求: 满足CAT. 5E(1000M) 标准。

d	MD	1	PBT UL94V-0	BLACK	
c	SHEEL	2	SUS201-1/2H	Ni PATING	
b	TERMINAL	8	C5191R-H	Au PATING	
a	HOUSING	2	PBT UL94V-0	BLACK	
NO.	PART NAME	QTY	MATERIAL	PLATING & COLOR	Remark

UNLESS OTHERWISE SPECIFIED TOLERANCES

DECIMALS:	ANGLES:
X : ±0.30	X : ±3°
XX : ±0.15	XX : ±1'
XXX : ±0.10	

SCALE: 1/1 UNIT: mm DWG. NO:

SIZE: A4	PAGE: 1 OF 1	REV: A02
APPROVED BY	CHECKED BY	PREPARED BY
DICK	YSH	YST

东莞市合陵电子有限公司
DongGuan Heling Electronic Co.,LTD