








CATEGORY	DESCRIPTION	P/N #
CONNECTOR	USB 3.0 AF DIP型沉板III.36(长端脚)	UB31F-XX11-HLRX21P-X

REV.	ECN NO.	DESCRIPTION	REVISED	DATE
A01		New Release	XSY	2020.03.06



Tolerance:  $\pm 0.05$  Thickness:  $1.0 \sim 1.2\text{mm}$   
 Recommend PCB Layout  
 (Top View)



UB31F-XX11-HLRX21P-X

X	Terminal Plating
0	Au 1u" Plating
1	Au 3u" Plating
2	Au 6u" Plating
3	Au 15u" Plating

X	Terminal Plating
B	Black
U	Blue 300C

X	Terminal Plating
G	SUS
B	Copper Alloy
S	SPCC

X	Shell Material
C	SUS
B	Copper Alloy
S	SPCC

X	Housing Color
B	Black
U	Blue 300C

X	包装方式
C	载带包装
P	吸塑包装

X	Terminal Plating
G	SUS
B	Copper Alloy
S	SPCC

UNLESS OTHERWISE SPECIFIED TOLERANCES

SCALE: 1/1 UNIT: mm

c	Shell	1	See Table T=0.3mm	Ni Plating
b	Terminal	9	Copper Alloy T=0.2mm	See Table
a	Housing	1	LCP UL94V-0	See Table
NO.	PART NAME	QTY	MATERIAL	PLATING & COLOR

DECIMALS:	ANGLES:	APPROVED BY	CHECKED BY	PREPARED BY
X : ±0.5	X : ±2°	Tony	XSY	XSY
XX : ±0.3	XX : ±1°			
XXX : ±0.2				

  
 东莞市合陵电子有限公司  
 Dongguan Heling Electronic Co., LTD  
 Connector

CUSTOMER COPY