




REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	BATCH PRODUCTION INITIAL RELEASE.	2018.11.21	郭丙建




Dim.D	NOTE
5.00mm	02pins
6.00mm	03~08pins
8.50mm	09~40pins

Specifications


Current Rating:3Amp
 Insulation Resistance:1000MΩMin.
 Dielectric Withstanding Voltage:600VAC
 Contact Resistance:20mΩMax.
 Operating Temperature:-40°C to +105°C
 Materials
 Contact Material: Brass
 Insulator Material:High Temperature Thermoplastic, UL 94V-0 Nylon 6T(Halogen Free) or the equivalent material
 All materials must meet Greenconn hazardous substances control standards.



Recommended P.C.Board Layout
(Tolerance:±0.05)



Ordering Information



格菱股份有限公司
Greenconn Corporation

GENERAL TOLERANCE	
X.*±5.0°	X.±0.30
.X*±3.0°	.X±0.25
.XX*±2.0°	.XX±0.15
.XXX*±1.0°	.XXX±0.10

DESIGNED: 郭丙建	DATE: 2018.11.21
CHECKED: 林煌隆	DATE: 2018.11.21
CO SIGNED: 廖世龍	DATE: 2018.11.21
APPROVED: 陳義昌	DATE: 2018.11.21

DWG. NO.	GPHC201-CB157RH
PART NO.	GPHC201-XXXX B157R1HX

TITLE.	2.54 PIN HEADER DUAL ROWS SMT TYPE CONNECTOR
--------	--

REV.	UNIT.	SCALE.	PAGE.
01	mm	4:1	1/1