

Specifications

备注 (Remark)

1. 材料 (MATERIAL)

胶芯: PA9T无卤+30%G.F UL94V-0, 颜色: 黑色.
 Housing: PA9T无卤+30%G.F UL94V-0, Color: Black
 端子: 青铜, 镍底30u"MIN, 表面镀高温亮锡
 Contact: Bronze, BRIGHT TIN-PLATED HIGH-TEMPERATURE OVER ALL
 30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 3 AMP
 Raring Current: 3 AMP.
 接触电阻: 20 mΩ MAX.
 Contact Resistance: 20 mΩ MAX.
 绝缘电阻: 1000 MΩ MIN.
 Insulating Resistance: 1000 MΩ MIN.
 耐电压: AC 500V/分钟.
 Withstanding Voltage: AC 500V/Minute.
 温度范围: -40° C to +105° C
 Temperature Range: -40° C to +105° C



客编: K5005

1. 带*为品质检验尺寸



注意事项

Ordering Information

F136-11 04 S3 C MU B 2

NO. OF PINS PER ROW 1-40P
 CONTACT PLATING Full Of Gold
 INSULATOR MATERIAL: Semi-gold
 PACKING TYPE: A: PE Bag, B: Tape & Reel, C: Tube, D: Tube+CAP, E: Tray

注: 同系列成品共用此图



东莞市宇熙精密连接器有限公司
 Dongguan Yuxi Electronic Co., Ltd.
 F136-1104S3CMUB2
 2.54间距 3.6mm螺距 1*4P SMT: 4.6 正插位 (型)
 无卤 (PA9T) 镀高温亮锡 麦拉+T200卷装 K5005

www.yxcon.com
 秦星宇 2020.07.24
 7.24

DESIGN A4
 CHECK 1/1
 APPROVE

OPERATION X.X ±0.25
 X.XX ±0.20
 X.XXX ±0.10
 Angle ±3°
 DIM TOL

SCALE UNIT MM
 SIZE A4
 SHEET 1/1
 PROJ. 6

Fit
 DESIGN 3.70±0.25mm
 MODIFICATION DESCRIPTION
 新版发行

PART NO. F136-1104S3CMUB2
 TITLE: 2.54间距 3.6mm螺距 1*4P SMT: 4.6 正插位 (型)
 Customer No.

REV DATE SYMBOL