

Specifications

备注(Remark)

1. 材料(MATERIAL)

胶芯: PA6T+30%G.F UL94V-0, 颜色:黑色.
Housing:PA6T+30%G.F UL94V-0, Color:Black
端子: 青铜, 镍底30u"MIN, 表面镀普金

Contact:Bronze, GOLD PLATING OVER ALL
30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 3 AMP

Raring Current:3 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance:20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.

Insulating Resistance:1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage:AC 500V/Minute.






温度范围: -40° C to+105° C

Temperature Range: -40° C to+105° C

Ordering Information

F168-12 15 A0 B SQ C 3

HEIGHT OF HOUSING	NO. OF PINS PER ROW	Full Of Gold	Semi-gold	INSULATOR MATERIAL:	PACKING
60:6.0mm	2-40P	A0=0.8u"	B0=0.8u"	A:PBT	A:PE Bag
68:6.8mm		A1=1u"	B1=1u"	B:PA6T	B:Tape & Reel
		A2=1.5u"	B2=1.5U"	C:PA9T	C:Tube
		A3=2u"	B3=2U"	D:LCP	D:Tube+CAP
		A4=3u"	B4=3U"		E:Tray
		A5=5u"	B5=5U"		
		A6=10u"	B6=10U"		
		A7=15u"	B7=15U"		
		A8=20u"	B8=20U"		
		A9=30u"	B9=30U"		
		S1=Ordinary Tin Plated			
		S2=Matte Tin Plated			
		S3=Tin-plated High-temperature			



RoHS COMPLIANT

注意事项

- 带*为品质重点检验尺寸
 - 堵
1. 2. 29. 30PIN

			OPERATION	SCALE	Fit	Yxcon 东莞市宇熙精密连接器有限公司		
			X.X ±0.25	UNIT	MM	www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd.		
			X.XX ±0.20	SIZE	A4	DESIGN	PART NO.	F168-1215A0BSQC3
A0	2022.02.24	/	X.XXX ±0.10	SHEET	1/1	CHECK	李官森2022.02.24	TITLE: 2.54排母6.8mm型高 2*15P 180度 带凸点上插式 四面包端子 PA6T料 镀普金 堵第1.2.29.30P 16个/管
REV	DATE	SYMBOL	Angle ±3°	DIM	TOL	PROJ.	APPROVE	Customer No.
新板发行								