




# Specifications

备注(Remark)  
 1. 材料(MATERIAL)  
 胶芯: PBT+30%G.F UL94V-0, 颜色:黑色.  
 Housing:PBT+30%G.F UL94V-0, Color:Black  
 端子: 青铜, 镍底30u"MIN, 表面镀普金  
 Contact:Bronze, GOLD PLATING OVER ALL  
 30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):  
 额定电流: 3 AMP  
 Rating Current:3 AMP.  
 接触阻抗: 20 mΩ MAX.  
 Contact Resistance:20 mΩ MAX.  
 绝缘阻抗: 1000 MΩ MIN.  
 Insulating Resistance:1000 MΩ MIN.  
 耐电压: AC 500V/分钟.  
 Withstanding Voltage:AC 500V/Minute.  
 温度范围: -40° C to+105° C  
 Temperture Range: -40° C to+105° C



# Ordering Information

F185-11 08 A0 A SU E 4

NO. OF PINS PER ROW	Contact Plating		INSULATOR MATERIAL:	PACKING
1-40P	Full Of Gold	Semi-gold	A: PBT	A: PE Bag
	A0=0.8u"	B0=0.8U"	B: PA6T	B: Tape & Reel
	A1=1u"	B1=1U"	C: PA9T	C: Tube
	A2=1.5u"	B2=1.5U"	D: LCP	D: Tube+CAP
	A3=2u"	B3=2U"		E: Tray
	A4=3u"	B4=3U"		
	A5=5u"	B5=5U"		
	A6=10u"	B6=10U"		
	A7=15u"	B7=15U"		
	A8=20u"	B8=20U"		
	A9=30u"	B9=30U"		
	S1=Ordinary Tin Plated			
	S2=Matte Tin Plated			
	S3=Tin-plated High-temperature			

RoHS COMPLIANT

客编: K8002

注意 事项  
 1. 带\*为品质重点检验尺寸



			OPERATION	SCALE	Fit	Yxcon 东莞市宇熙精密连接器有限公司					
			X.X ±0.25	UNIT	MM	www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd.					
			X.XX ±0.20	SIZE	A4	DESIGN	PART NO.	F185-1108A0ASUE4			
A0	2021.09.23	/	X.XXX ±0.10	SHEET	1/1	CHECK	李官森2021.09.23	TITLE:	2.54排母8.5mm型高 1*8P 180度 DIP:3.5 型宽=3.0mm O型A款 PBT料 镀普金 300/盒		
REV	DATE	SYMBOL	Angle ±3°	PROJ.	APPROVE	Customer No.	2021.9.23				
			DIM TOL								