

Specifications

Ordering Information




F185-11 22 A0 A SU C 2

备注(Remark)
 1. 材料(MATERIAL)
 胶芯: PBT+30%G.F UL94V-0, 颜色: 黑色.
 Housing: PBT +30%G.F UL94V-0, Color: Black
 端子: 青铜, 银底30u"MIN, 表面镀普金
 Contact: Bronze, GOLD PLATING OVER ALL
 30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):
 额定电流: 3 AMP
 Rating Current: 3 AMP.
 接触阻抗: 20 mΩ MAX.
 Contact Resistance: 20 mΩ MAX.
 绝缘阻抗: 100 MΩ MIN.
 Insulating Resistance: 1000 MΩ MIN.
 耐电压: AC 500V/分钟.
 Withstanding Voltage: AC 500V/Minute.
 温度范围: -40° C to +105° C
 Temperature Range: -40° C to +105° C

NO. OF PINS PER ROW	Contact Plating	INSULATOR MATERIAL	PACKING
1-40P	Full Of Gold	A: PBT	A: PE Bag
	Semi-gold	B: PA6T	B: Tape & Reel
		C: PA9T	C: Tube
		D: LCP	D: Tube+CAP
			E: Tray


S1=Ordinary Tin Plated
 S2=Matte Tin Plated
 S3=Tin-plated High-temperature



RoHS COMPLIANT

客编: K8002

注意事项
 1. 带*为品质重点检验尺寸



			OPERATION		SCALE		Fit		Yxcon 东莞市宇熙精密连接器有限公司	
			X.X	±0.25	UNIT		MM		www.yxcon.com Dongguan Yuxi Electronic Co., Ltd.	
			X.XX	±0.20	SIZE	A4	DESIGN	李官森 2021.09.27	PART NO.	F185-1122A0ASUC2
A0	2021.09.27	/	新版发行		SHEET	1/1	CHECK	刘伟 9.27	TITLE:	2.54排母 8.5mm 型高 1*22P 180度 型宽=3.0mm
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION		PROJ.	APPROVE		Customer No.	O型A款 PBT料 镀普金 90/盒	