

Specifications

备注 (Remark)
 1. 材料 (MATERIAL)
 胶芯: PA6T+30%G.F UL94V-0, 颜色: 黑色.
 Housing: PA6T+30%G.F UL94V-0, Color: Black
 端子: 青铜, 镍底30u"MIN, 表面镀金3u"MIN
 Contact: Phosphor bronze, 3u"MIN GOLD PLATING OVER ALL
 30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):
 额定电流: 3 AMP
 Rating Current: 3 AMP.
 接触阻抗: 20 mΩ MAX.
 Contact Resistance: 20 mΩ MAX.
 绝缘阻抗: 1000 MΩ MIN.
 Insulating Resistance: 1000 MΩ MIN.
 耐电压: AC 500V.
 Withstanding Voltage: AC 500V.
 温度范围: -40° C to +105° C
 Temperature Range: -40° C to +105° C

工程部
 2020.01.14
 受控文件





Ordering Information

F185-12 09 A4 B MU B 4

NO.OF PINS PER ROW 2-40P	Full Of Gold	Semi-gold	INSULATOR MATERIAL:	PACKING
A0=0.8u"	B0=0.8U"	B:PA6T	A:PE Bag	B:Tape & Reel
A1=1u"	B1=1U"	C:PA9T	C:Tube	D:Tube+CAP
A2=1.5u"	B2=1.5U"	D:LCP	E:Tray	
A3=2u"	B3=2U"			
A4=3u"	B4=3U"			
A5=5u"	B5=5U"			
A6=10u"	B6=10U"			
A7=15u"	B7=15U"			
A8=20u"	B8=20U"			
A9=30u"	B9=30U"			
S1=Ordinary Tin Plated				
S2=Matte Tin Plated				
S3=Tin-plated High-temperature				

空7.8PIN



				OPERATION	SCALE	Fit	东莞市宇熙精密连接器有限公司 Dongguan Yuxi Electronic Co.,Ltd.			
				X.X ±0.25	UNIT	MM				
				X.XX ±0.20	SIZE	A4	DESIGN	杨哲	PART NO.	F185-1209A4BMUB4
				X.XXX ±0.10	SHEET	1/1	CHECK		TITLE:	2.54mm排母 型高8.5 2*9P 镀3u"金 PA6T料 SMT:8.2 传统U型 带柱 CAP+卷装 K-7.8P
				Angle ±3°	PROJ.	APPROVE		Customer No.	EM216254F1SB	
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	APPROVE						